


# EA&SM

## 常规柱塞泵 | 微型柱塞泵



 恒永达


- 准确性ACC<0.5% (100%);
- 重复性CV<0.5% (100%);
- 寿命长达500万次;
- 量程范围50 $\mu$ L~20mL;
- 泵阀一体化设计;
- 采用SMC电磁阀,质量稳定可靠。



集成SMC电磁阀



精密陶瓷柱塞




可配置控制系统



深圳市恒永达科技股份有限公司  
地址：深圳市南山区西丽沙河西路百旺研发大厦16楼  
联系方式：+86 180 3305 0011 (微信同)  
关注公众号查看产品详细信息

## EA\常规柱塞泵

量程	μL	50	100	250	500	1000	2500	5000	10000	20000
分辨率	μL/Step	0.025	0.05	0.125	0.25	0.5	1.12	2.5	2.5	2.5
泵类型	\	柱塞式								
柱塞	\	陶瓷								
装配尺寸	mm	2×M3×31.8 or 2×M3×42.8								
螺纹	N/A	2×1/4-28UNF or 2×M6,平底接口								
背隙	%	<1.0%								
准确性-100%行程	%	<0.5%								
重复性-100行程	%	<0.5%								
寿命	Cycles	5,000,000								
流体压力	MPa	<0.30								



## SM\微型柱塞泵

量程	μL	50	100	250	500	1000
分辨率	μL/Step	0.025	0.05	0.125	0.25	0.5
泵类型	\	柱塞式				
柱塞	\	陶瓷				
装配尺寸	mm	4×M3 - 15×35				
螺纹	N/A	2×1/4-28UNF or 2×M6,平底接口				
背隙	%	<1.0%				
准确性-100%行程	%	<0.5%				
重复性-100行程	%	<0.5%				
寿命	Cycles	5,000,000				
流体压力	MPa	<0.30				